

600mm x 300mm, Breadboard



Stock **#54-641** 20+ In Stock

-

1

+

€380^{.07}

ADD TO CART

Volume Pricing	
Qty 1+	€380,07 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Metric

Physical & Mechanical Properties

Thickness (mm):

13.00

600.00	Length (mm):
300.00	Width (mm):
Black Anodized Aluminum	Construction:
0.18mm per 300mm	Flatness (mm):
6.1	Weight (kg):
288.00	Number of Holes:

Threading & Mounting

Mounting Threads:
(288) M6 x 1.0 on 25 Centerline ±0.025mm, on 12.5mm Corners

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

PRODUCT DETAILS

- Provide Stable Platform for Experiments and Test Configurations
- 1/4-20 TPI or M6 Tapped Holes for Various Mounting
- Black Anodized Aluminum

English and Metric Breadboards utilize 1/4"-20, or M6 tapped holes spaced 1" and 25mm apart, respectively, allowing for the creation of customizable benchtop systems. These breadboards are compatible with most optics and photonics mounting solutions. They feature a black anodized finish which reduces reflections from the breadboard and back into the system. English and Metric Breadboards are available in multiple sizes, making it possible to create either compact or large, expansive systems. These breadboards are an ideal platform for any system application.