

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #86-201 ☐ In Stock



1



€515,00

ADD TO CART

Qty 1-5

€515,00

Qty 6+

€436,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Extinction Ratio:

9000:1

Substrate: ☐

[XP42-200 on PMMA](#)

Length (mm):

900.00

Operating Temperature (°C):

-40 to +80
Dimensions (mm): 600.0 x 900.0 +0.0/-3.0
Thickness (mm): 2.22 ±0.25
Transmission (%): Single: 42 Parallel: 36 Crossed: <0.004
Type: Linear Polarizer
Construction: Polarizing Film on PMMA
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98
Width (mm): 600.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant