

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6.0mm Diameter X -12 FL, MgF2 Coated, Plano-Concave Lens



Stock #45-009 3-4 DAYS
[Other Coating Options](#)

1 €34,00

ADD TO CART

Qty 1-9
€34,00
Qty 10+
€30,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-12.00
Substrate: ☐ N-BK7
f#: 2.00
Numerical Aperture NA: 0.25
Coating: MgF₂ (400-700nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -12.99
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 5.4
Coating Specification: R_{avg} ≤1.75% @ 400 - 700nm
Edge Thickness ET (mm): 2.12
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -6.20
Surface Quality: 40-20
Damage Threshold, By Design: ☐ 10 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant