

## 60mm sq - Rectangular Bar Clamp



Stock #54-995 **20+ In Stock**

- 1 + €126<sup>.00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€126,00 each
Qty 10-25	€113,40 each
Qty 26-49	€107,10 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Fixed **Type:**

Square or Rectangular **Type of Optics:**

Available in Quick Start Kit: [#17-529](#) **Note:**

## Physical & Mechanical Properties

**Construction:**  
Black Anodized Aluminum, Stainless Steel Post

**Edge Thickness of Compatible Optics (mm):**  
12.0 (Max)

## Threading & Mounting

**Size of Compatible Optics (mm):**  
5.0 - 60.0

**Compatible Post:**  
M6 x 1.0

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Contains SVHC\(s\)](#)

## Product Details

- Black Anodized Aluminum
- M6 x 1.0 Mounting Thread
- [Posts](#) and [Post Holders](#) Required for Mounting

Metric Rectangular Optic Mounts have a bar-type design with non-marring mounting surfaces, making it ideal for rectangular optics such as filters and mirrors, as well as cylindrical lenses. The mounts are available in 25 or 60mm sq for rectangular or square optics. They are compatible with a M6 x 1.0 mounting thread. Metric Rectangular Optic Mounts are constructed of black anodized aluminum with a stainless-steel post. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

## Technical Information

A	B	C	D	E	F	G	H	Stock No.
30	25	40	48	12	10	1.0	8.5	<a href="#">#54-994</a>
60	60	85	95	14	15	1.5	12	<a href="#">#54-995</a>

