

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6.25mm Dia X -25mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #47-745 3-4 DAYS

1

€59,50

ADD TO CART

Qty 1-5
€59,50

Qty 6+
€47,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.2

Effective Focal Length EFL (mm):
-25.00

Substrate: ☐
[N-BK7](#)

f/#: 4.00
Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -26.31
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 2.38
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -12.92
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View