

[See all 11 Products in Family](#)

6.5mm Travel, 0.002mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock #33-738 **1 In Stock**

⊖ 1 ⊕ €176⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	€176,00 each
Qty 10-24	€158,40 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Metric **Type:**
Mtutoyo **Manufacturer:**

Physical & Mechanical Properties

6.5 **Travel (mm):**

0.002	Graduation (mm):
9.5	Stem Diameter (mm):
Plain/Spherical	Stem/Spindle:
9.5	Stem Length (mm):
5	Spindle Diameter (mm):
14	Min. Spindle Length (mm):
13	Max. Diameter (mm):
55	Overall Length (mm):

Hardware & Interface Connectivity

Metric Micrometer	Type of Drive:
-------------------	----------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.