

676nm CWL, 11.8mm Dia. Bandpass Filter



Stock **#28-484** CLEARANCE 3-4 DAYS

-

1

+

€19,95

ADD TO CART

Qty 1+
€19,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm): 11.80
Optical Density OD (Average): ≥3.0
Center Wavelength CWL (nm): 676.00
Center Wavelength CWL Tolerance (nm): ±2
Full Width-Half Max FWHM (nm): 10.00

Minimum Transmission (%): 50
Surface Quality: 80-50
Thickness (mm): 4.60
Type: Bandpass Filter
Typical Applications: Kr Emission Line
Blocking Wavelength Range (nm): 200 - 1200
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View