

6.96mm FL, High Resolution, f/1.6, Micro Video Lens



Stock #11-326 3-4 DAYS

- 1 + **€74,00**

ADD TO CART

Qty 1-49
€74,00
Qty 50+
€57,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm): 25.24
Maximum Diameter (mm): 19.0
Maximum Image Circle (mm): 9.00
Horizontal Field of View @ Max Sensor Format:

63.2
Resolution, On-Axis: 100 lp/mm @ 63.4% Contrast
Resolution, 0.7 Field: 100 lp/mm @ 55.9% Contrast
Resolution, Full Field: 100 lp/mm @ 39.5% Contrast
Note: High Resolution
TV Distortion (%): -11.2
Type: M12 Imaging Lens
Focal Length FL (mm): 6.96
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/1.6
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View