

6.96mm FL, High Resolution, f/1.6, Micro Video Lens



Stock **#17-160** [CONTACT US](#)

- 1 + **€74,00**

ADD TO CART

Qty 1-49
€74,00
Qty 50+
€57,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
29.60

Maximum Diameter (mm):
19

Maximum Image Circle (mm):
8.00

Note:

High Resolution
Type: M12 Imaging Lens
Focal Length FL (mm): 6.96
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/1.6
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

Certificate of Conformance: View
--