

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

69mm Outer Dia., Zero Aperture, Burnished Steel Leaves



Zero Series

Stock #57-591 3-4 DAYS



1



€175,00

ADD TO CART

Qty 1-4

€175,00

Qty 5+

€154,70

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
40.0

Outer Diameter (mm):
69.0

Construction: Anodized Aluminum Alloy, Burnished Leaves
Full Angular Range of Lever (°): 96.00
Lever Length (mm): 16.00
Lever Position (mm): 3.3
Lever Size (mm): 6.00 x 1.50
Number of Leaves: Two sets of 7
Operating Temperature (°C): <250
Pin Thread & Pitch: N/A
Thickness (mm): 6.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant