

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6mm Dia. x 24mm FL Uncoated, Double-Convex Lens



Stock #32-867 ☐ In Stock
[Other Coating Options](#)

1 €28,50

ADD TO CART

Qty 1-9
€28,50
Qty 10+
€25,75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Back Focal Length BFL (mm):

23.13
Effective Focal Length EFL (mm): 24.00
Coating: Uncoated
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.60
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.23
Radius R ₁ =R ₂ (mm): 24.36
Clear Aperture CA (mm): 5.4
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant