

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6mm Dia. X 24mm FL, VIS-NIR, Inked, Double-Convex Lens



Stock #45-863-INK 3-4 DAYS

1 €52,00

ADD TO CART

Qty 1-9

€52,00

Qty 10+

€46,75

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00

Back Focal Length BFL (mm):
23.13

Effective Focal Length EFL (mm): 24.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.60
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.23
Radius R₁=R₂ (mm): 24.36
Clear Aperture CA (mm): 5.4
f/#: 4.00
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View