

## 6mm Dia. x 6mm FL, Commercial Grade, Double-Convex Lens



Stock **#27-722** CLEARANCE ☐ In Stock

-

1

+

**€14,95**

ADD TO CART

Qty 1+

€14,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Diameter (mm):**  
6.00 +0.00/-0.10

**Back Focal Length BFL (mm):**  
5.00

**Effective Focal Length EFL (mm):**  
6.00

**Coating:**  
Uncoated

**Substrate:** ☐  
N-SK18

|                                                      |
|------------------------------------------------------|
| Centering (arcmin):<br>6.00                          |
| Center Thickness CT (mm):<br>3.00                    |
| Center Thickness Tolerance (mm):<br>±0.10            |
| Edge Thickness ET (mm):<br>1.65                      |
| Radius R <sub>1</sub> (mm):<br>7.02                  |
| Clear Aperture CA (mm):<br>≥5.1                      |
| f##:<br>1.00                                         |
| Focal Length Specification Wavelength (nm):<br>587.6 |
| Focal Length Tolerance (%):<br>±1                    |
| Numerical Aperture NA:<br>0.5                        |
| Type:<br>Double-Convex Lens                          |
| Wavelength Range (μm):<br>0.38 - 2.2                 |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |