

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6mm Dia. X -12mm FL, Uncoated, Double-Concave Lens



Stock #48-681 3-4 DAYS

[Other Coating Options](#)

1 €27,50

ADD TO CART

Qty 1-9

€27,50

Qty 10+

€24,75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-12.00
Substrate: N-BK7
f#: 2.00
Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Double-Concave Lens
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -12.33
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 5.4
Edge Thickness ET (mm): 1.59
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -12.57
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View