

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6mm Dia. X -6mm FL, VIS 0⁺, Inked, Double-Concave Lens



Stock #47-914-INK [CONTACT US](#)

[Other Coating Options](#)

1 **€48,50**

ADD TO CART

Qty 1-9

€48,50

Qty 10+

€43,75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Effective Focal Length EFL (mm):

-6.00
Substrate: NSF11
f#: 1.00
Numerical Aperture NA: 0.50
Coating: VIS 0° (425-675nm)
Type: Double-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -6.41
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.4
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 2.29
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -9.74
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View