


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6" Dia. Enhanced Aluminum, λ /20 Flat Fused Silica



Stock #47-575-533 3-4 DAYS

1 €2.769,00

ADD TO CART

Qty 1-5

€2.769,00

Qty 6+

€2.492,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 λ /20 (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 152.40 +0.0/-1.02
Diameter Tolerance (inches): +0.0/-0.04
Substrate: ☐ Fused Silica (Corning 7980)
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 137.16
Note: Flatness is specified as Peak to Valley
Thickness (mm): 25.40 ±2.0
Thickness Tolerance (mm): ±2.0
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant