

700nm CWL, 80nm FWHM, 12.5mm Mounted Diameter



Stock #65-738 ☐ In Stock

[Additional Bandwidths](#)



1



€89,00

ADD TO CART

Qty 1-9

€89,00

Qty 10+

€80,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):

≥3.0
Clear Aperture CA (mm): 9.0
Center Wavelength CWL (nm): 700.00 ±15
Center Wavelength CWL Tolerance (nm): ±15
Full Width-Half Max FWHM (nm): 80.00 ±25
Full Width-Half Max FWHM Tolerance (nm): ±25
Minimum Transmission (%): ≥60
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: Clinical Chemistry
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View