

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 70mm, 180mm Radius, English Goniometer



70mm, 180mm Radius, English Goniometer

Stock #66-534 3-4 DAYS



1



€727,00

ADD TO CART

Qty 1-2

€727,00

Qty 3+

€636,60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:
English

Stage Size (mm): 70 x 70
Travel (°): ±8
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 6
Mounting Threads: (9) 1/4-20, (4) 6-32, (8) 2-56
Radius R (mm): 180
Resolution (arcmin): 5
Stage Size (inches): 2.75 x 2.75
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
