

TECHSPEC® 70mm, Side Drive, Standard Top, English Extended Micrometer



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



Stock **#66-431** 3-4 DAYS

⊖ 1 ⊕

€487,00

ADD TO CART

Qty 1-2

€487,00

Qty 3+

€425,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive: English Micrometer
Drive Orientation: Side Drive
Type: English
Stage Size (mm): 70 x 70
Travel (inches): 1
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 8
Mounting Threads: (8) 1/4-20, (4) 6-32, (8) 2-56
Stage Size (inches): 2.75 x 2.75
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)