

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 70mm, Side Drive, Standard Top, English Stage



70mm, Side Drive, Solid Top Stage

Stock #66-429 3-4 DAYS



1



€399,00

ADD TO CART

Qty 1-2

€399,00

Qty 3+

€348,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Lead Screw

Drive Orientation: Side Drive
Type: English
Stage Size (mm): 70 x 70
Travel (inches): 0.5
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 8
Mounting Threads: (8) 1/4-20, (4) 6-32, (8) 2-56
Stage Size (inches): 2.75 x 2.75
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
