

70mm Sq. Metric Kinematic Magnetic Base



#22-404: 70mm Sq. Metric Kinematic Magnetic Base

Stock **#22-404** **1 In Stock**

⊖ 1 ⊕ €154⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	€154,00 each
Qty 10+	€139,30 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Metric

Switchable:
No

Physical & Mechanical Properties

Length (mm):
70.00

70.00	Width (mm):
25.40	Thickness (mm):
Anodized Aluminum	Construction:
0.27	Weight (kg):
<70.0	Repeatability (µrad):

Threading & Mounting

(8) M4 x 0.7, (11) M6 x 1.0	Mounting Threads:
-----------------------------	--------------------------

Material Properties

20	Magnetic Force (N):
----	----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.