

70mm Travel, X-Y Positioning Table



70mm Travel, X-Y Positioning Table, #39-930

Stock **#39-930** 3-4 DAYS

⊖ 1 ⊕

€764,00

ADD TO CART

Qty 1+

€764,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X-Y)

Guide System:
Dovetail

Type of Drive:
Rack and Pinion

Drive Orientation:
Center Drive

Type:

Universal (No Holes)
Stage Size (mm): 100 x 100
Travel (mm): 70 (±35mm) in X and Y
Travel (inches): 2.75 (±1.37) in X and Y
Construction: Black Anodized Aluminum
Height (mm): 45
Load Capacity, Normal (kg): 10
Note: Top plate 100mm sq., while bottom plate is 100mm dia.
Travel Per Knob Rotation (mm): 18
Weight (kg): 0.83

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View