

70mm Travel, X-Y Positioning Table



70mm Travel, X-Y Positioning Table, #39-930

Stock **#39-930** 20+ In Stock

-

1

+

€818⁸⁵

ADD TO CART

Volume Pricing	
Qty 1+	€818,85 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Universal (No Holes)

Type:

Note:
Top plate 100mm sq., while bottom plate is 100mm dia.

Physical & Mechanical Properties	
Linear (X-Y)	Type of Movement:
Dovetail	Guide System:
Center Drive	Drive Orientation:
100 x 100	Stage Size (mm):
70 (±35mm) in X and Y	Travel (mm):
2.75 (±1.37) in X and Y	Travel (inches):
Black Anodized Aluminum	Construction:
45	Height (mm):
10	Load Capacity, Normal (kg):
18	Travel Per Knob Rotation (mm):
0.83	Weight (kg):
Hardware & Interface Connectivity	
Rack and Pinion	Type of Drive:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- 70mm (±35mm) Travel in Both X and Y
- Rack and Pinion Movements for Fast Adjustment
- Solid Top Design

X-Y Positioning Tables are ideal platforms for fast and easy positioning in both X and Y-axes. The 70mm Travel, Rack and Pinion, X-Y Axis Positioning Table uses two stacked rack and pinion movements for more precise positioning. The 70mm Travel Table can support a normal load of up to 10kg. X-Y Positioning Tables work well in labs where parts or systems need to be moved freely and often. The top platform and bottom platform of the 70mm Travel Table are removable via (4) M4 screws and can be positioned in either orientation.

TECHNICAL INFORMATION

