

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Richardson Gratings™ 75 Grooves, 12.7 X 12.7mm, 10µm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #15-769 3-4 DAYS



1



€131,00

ADD TO CART

Qty 1+

€131,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
75

Wavelength Range (nm):
7000 - 16000

Blaze Wavelength (nm):

10000 ±25
Blaze Angle (°): 22
Peak Efficiency, Typical (%): 77 (5th order)
Dimensions (mm): 12.7 x 12.7 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 12.70
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 12.70
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: Unpolarized
Master Reference: 1104
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View