

SCHOTT KG1, 75mm Sq., 3mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#45-721** 3-4 DAYS

⊖ 1 ⊕ **€170,00**

ADD TO CART

Qty 1-10

€170,00

Qty 11+

€149,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
75.0 x 75.0

Density (g/cm³):
2.53

Glass/Filter Number:

[SCHOTT KG1](#)

Substrate: ☐
Heat Absorbing Glass

Length (mm):
75.00

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d :
1.51

Surface Quality:
60-40

Transformation Temperature (°C):
599

Thickness (mm):
3.00 ±0.38

Type:
IR Cut-Off Filter

Width (mm):
75.00

Dimensional Tolerance (mm):
±0.25

Reflection Factor P_d :
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)