

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT



MgF₂ Coated Achromatic Lenses



Stock **#33-919-INK** [CONTACT US](#)

[Other Coating Options](#)



1



€310,00

ADD TO CART

Qty 1-5

€310,00

Qty 6+

€248,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
75.00 ±0.025

Effective Focal Length EFL (mm): 150.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 126.46
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 73.5
Centering (arcmin): <1
Center Thickness CT (mm): 46.30 ±0.20
Center Thickness CT 1 (mm): 23.20 ±0.10
Center Thickness CT 2 (mm): 23.10 ±0.10
Radius R₁ (mm): 92.05
Radius R₂ (mm): -72.85
Radius R₃ (mm): -305.87
Edge Thickness ET (mm): 36.01
Substrate: ☐ N-BAK1 / N-SF8
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View