

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

75mm Diameter x 50mm FL , Aspneric Condenser Lens



Stock #46-244 ☐ In Stock

[Other Coating Options](#)



1



€91,00

ADD TO CART

Qty 1-10

€91,00

Qty 11+

€80,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
75.00 +0.0/-0.5

Effective Focal Length EFL (mm):
50.00

Numerical Aperture NA:
0.75

Back Focal Length BFL (mm): 30.50
Substrate: B270
Focal Length Tolerance (%): ±7
Coating: Uncoated
Centering (arcmin): ≤20
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 72
Edge Thickness ET (mm): 3.0
Center Thickness CT (mm): 30.00 ±0.50
f/#: 0.7
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 75.0
Radius R ₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View