

75mm Width, Dovetail Carrier



75mm Width, Dovetail Carrier, #55-340

Stock **#55-340** **1 In Stock**

-

1

+

€126⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€126,69 each
Qty 5+	€118,55 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Metric

Type:


Note:

Carrier	
Physical & Mechanical Properties	
Linear (X)	Type of Movement:
Dovetail	Guide System:
3	Length (inches):
76.20	Length (mm):
Black Anodized Aluminum	Construction:
Hardware & Interface Connectivity	
Manual	Type of Drive:
Threading & Mounting	
(1) M16 x 1.0, (10) M4 x 0.7, (4) M3 x 0.5	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:


PRODUCT DETAILS

- Wide Range of Carrier Length and Mounting Hole Options Available
 - Low Profile Design with Smooth Movement
 - Increased Stability and <1mrad Straight Line Accuracy
- Dovetail Optical Rail Systems are designed for easy and stable installation and positioning of various optical components along the same axis. The rails feature slotted holes that allow them to be fixed to standard 1/4-20 TPI and M6 breadboards or optical tables. Carriers are available with different lengths and hole patterns to meet various mounting needs including options that are directly compatible with our TECHSPEC® Manual Stages for precision alignment. Carriers utilize a unique two-piece design to prevent the locking screws from contacting the rail and to allow easy attachment and removal. All Dovetail Optical Rail System parts are constructed of black anodized aluminum to minimize stray reflections or glare.
- Note:** Rails and carriers are sold separately.

TECHNICAL INFORMATION



Common Side Profile



Stock No.	L	A	B	C	D	# Slots	# C'bores
#54-401	12	6	4	—	—	3	—
#54-402	36	18	16	4	6	5	2

