

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

7.5X Mitutoyo Plan Apo Infinity Corrected Long WD Objective

See More by [Mitutoyo](#)



7.5X Mitutoyo Plan Apo Infinity Corrected Long WD Objective, #66-383

Stock **#66-383** 3-4 DAYS



1



€1.349,00

ADD TO CART

Qty 1+

€1.349,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Horizontal Field of View, 1/2" Sensor:
0.85mm

Horizontal Field of View, 2/3" Sensor:
1.17mm

Focal Length FL (mm):
26.67

Model Number: 378-807-3
Length excluding Threads (mm): 60.00
Magnification: 7.5X
Maximum Diameter (mm): 34
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.21
Mounting Threads: M26 x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 1.3
Depth of Field (µm): 6.20
Field of View, 24 Diameter Field Eyepiece (mm): 3.2
Field of View, 18 Diameter Field Eyepiece (mm): 2.4
Operating Temperature (°C): +5 to +40
Operating Humidity: 20 - 80%
Working Distance (mm): 35.0
Weight (g): 240.00
Wavelength Range (nm): 435 - 655
Style: Infinity Corrected
Manufacturer: Mitutoyo
Parfocal Length (mm): 95
Immersion Liquid: N/A
Exit Pupil Diameter (mm): 11.20

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)