

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



4-6λ First Surface Mirrors

Stock #69-252 CLEARANCE 3-4 DAYS



1



€38,00

ADD TO CART

Qty 1-5

€38,00

Qty 6+

€30,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):  
4 - 6λ

Substrate: ☐  
Float Glass

Surface Quality:  
80-50

|                                                                            |
|----------------------------------------------------------------------------|
| <div>Dimensions (mm):<br/>76.2 x 76.2 ±0.76</div>                          |
| <div>Coating Specification:<br/>R<sub>avg</sub> &gt;85% @400 - 700nm</div> |
| <div>Coating:<br/>Protected Aluminum (400-700nm)</div>                     |
| <div>Coating Type:<br/>Metal</div>                                         |
| <div>Angle of Incidence (°):<br/>45.00</div>                               |
| <div>Bevel:<br/>Protective as needed</div>                                 |
| <div>Clear Aperture (%):<br/>&gt;90</div>                                  |
| <div>Thickness (mm):<br/>6.00</div>                                        |
| <div>Type:<br/>Flat Mirror</div>                                           |
| <div>Wavelength Range (nm):<br/>400 - 700</div>                            |
| <div>Length (mm):<br/>76.20</div>                                          |
| <div>Width (mm):<br/>76.20</div>                                           |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |
| <div>Reach 233:<br/><a href="#">Compliant</a></div>             |

---