

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

76.2mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #69-251 3-4 DAYS



1



€38,00

ADD TO CART

Qty 1-5
€38,00

Qty 6+
€30,50

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
76.20 ±0.76

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality: 80-50
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
