

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 7 mm Max Aperture Motorizable Iris



High Performance Motorizable Iris



Stock #34-286 In Stock

- 1 +

€114,00

ADD TO CART

Qty 1-4

€114,00

Qty 5+

€100,70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
0.9

Maximum Aperture (mm): 7.0
Outer Diameter (mm): 12.0
Construction: Brass-Spring Steel
Number of Leaves: 8
Thickness (mm): 6.00
Pitch Diameter (mm): 9.94

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)

