

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



7X, 532nm LCHT Fixed YAG Beam Expander, #37-062

Stock #37-062 3-4 DAYS



1



€184,00

ADD TO CART

Qty 1-9

€184,00

Qty 10+

€163,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Coating:

VS 0° (425-675nm)

Design Wavelength DWL (nm):

532

Entrance Aperture (mm): 3.5
Exit Aperture (mm): 21
Expansion Power: 7X
Substrate: ☐ Optical Glass
Length (mm): 76.40
Mounting Threads: M22 x0.75
Transmission (%): >98 (nominal)
Type: Beam Expander
Weight (g): 74
Housing Diameter (mm): 29.95
Transmitted Wavefront, P-V: <λ/4 @ 532nm for Input Beam ≤1.4mm (by design)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Wavelength Range (nm): 532
Style: Fixed Magnification
Divergence Adjustment: None

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View