

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

80X Mitutoyo Plan UV Infinity Corrected Objective

See More by [Mitutoyo](#)



Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives

Stock #56-322 [CONTACT US](#)



1



€24.795,00

ADD TO CART

Qty 1+

€24.795,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Design Wavelength DWL (nm):
266, 532

Horizontal Field of View, 1/2" Sensor:
0.08mm

Horizontal Field of View, 2/3" Sensor:
0.11mm

Focal Length FL (mm): 2.50
Model Number: 378-839-5
Length excluding Threads (mm): 85.00
Magnification: 80X
Maximum Diameter (mm): 34
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.55
Mounting Threads: M26 x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (μm): 0.5
Depth of Field (μm): 0.90
Field of View, 24 Diameter Field Eyepiece (mm): 0.30
Field of View, 18 Diameter Field Eyepiece (mm): 0.23
Operating Temperature (°C): -5 to +45
Operating Humidity: 20 - 80%
Working Distance (mm): 10.0
Weight (g): 380.00
Note: Example Application: passivation (insulation films) of semiconductor circuits and repair of color filters of LCD panels (defect repair)
Style: Infinity Corrected
Manufacturer: Mitutoyo
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)