

81mm Dia., IR 940nm, Long WD High Intensity Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination Long Working Distance High Intensity Spot Lights

Stock **#18-607** 1 In Stock

-

1

+

€655^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€655,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

SL246-940IC

Model Number:

50000

LED Lifetime (hours):

LED Illuminator	Type of Illumination:
Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	Note:
Advanced Illumination	Manufacturer:
Spot Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
81.00	Diameter (mm):
575	Weight (g):
Optical Properties	
IR	Color:
940.00	Wavelength (nm):
Electrical	
0.40A	Minimum Input Current:
Hardware & Interface Connectivity	
Flying Leads	Connector:
24V	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
2	Length of Cable (m):
Environmental & Durability Factors	
0 - 60	Operating Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

PRODUCT DETAILS

- Even Illumination at Long Working Distances
- High Intensity Output up to 110,000 Lux
- Working Distances up to 2,700mm
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Advanced Illumination Long Working Distance High Intensity Spot Lights are designed for applications requiring intense illumination at long working distances. These spot lights feature 12 high current LEDs precisely focused to produce high brightness illumination at working distances from 300mm to 2,700mm. Advanced Illumination Long Working Distance High Intensity Spot Lights are available in a full range of wavelengths and are ideal for applications requiring small field of views and long working distances.

Note: Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.