

TECHSPEC® 825nm 25mm Diameter, OD 2.0 Shortpass Filter



TECHSPEC OD 2.0 Shortpass Filters

Stock **#64-647** CLEARANCE 3-4 DAYS



1



€126,00

ADD TO CART

Qty 1+

€126,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm):
825.00

Substrate: Fused Silica (Coming 7980)
Coating: Traditional Coated
Rejection Wavelength (nm): 880 - 1080
Surface Quality: 40-20
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.1
Transmission (%): >85
Transmission Wavelength (nm): 400 - 800
Type: Shortpass Filter
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Slope Factor (%): ±3
Cut-Off Tolerance (%): ±2
Wavelength Range (nm): 400 - 1080

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View