

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

60mm Max. Aperture, Burnished Steel Leaves Iris Diapnragm



Standard Series

Stock #57-585 3-4 DAYS



1



€203,00

ADD TO CART

Qty 1-4

€203,00

Qty 5+

€179,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
4.0, Typical

Maximum Aperture (mm):
60.0

Outer Diameter (mm): 82.0
Construction: Anodized Aluminum Alloy, Burnished Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 13.00
Number of Leaves: 17.00
Thickness (mm): 8.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant