

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

830 Grooves/mm, 25mm Sq, UV Transmission Grating Beamsplitter



Stock #85-294 3-4 DAYS



1



€232,50

ADD TO CART

Qty 1-9

€232,50

Qty 10+

€209,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
830

Wavelength Range (nm):
250 - 450

Blaze Angle (°):
19.4

Dimensions (mm): 25.00 x25.00
Construction: Blazed Grating
Length (mm): 25.00
Substrate: Fused Silica (Corning 7980)
Thickness (mm): 2.00 ±0.5
Type: Transmission Diffraction Grating
Width (mm): 25.00
Alignment of Grooves to Edge (°): ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View