

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 8" Nom. Uncoated, N-BK7 Wedge Prism



Stock #45-401 3-4 DAYS

1 €47,50

ADD TO CART

Qty 1-5
€47,50

Qty 6+
€38,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Angle Tolerance (arcsec):

±30

Bevel:

Protective bevel as needed

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 25.00 +0.00/-0.10
Image Orientation: Beam Deviation
Power (diopters): 14.05
Ray Deviation @ 633nm (°): 8.00
Substrate: N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 3.00
Type: Wedge Prism
Wavelength Range (nm): 350 - 2200
Wedge Angle: 14° 51'
Maximum Edge Thickness (mm): 9.6

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View