

8mm Dia. x 6.9mm FL, Small Diameter Plastic Aspheric Lens



Stock #14-572 3-4 DAYS

- 1 + **€32,00**

ADD TO CART

Qty 1-10
€32,00
Qty 11+
€26,50
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
8.00 ±0.20

Effective Focal Length EFL (mm):
6.90 @ 550nm

Numerical Aperture NA: 0.58
Back Focal Length BFL (mm): 6.11
Substrate: Acrylic V825
Focal Length Tolerance (%): ±1.5
Aspheric Design Wavelength (nm): 550
Coating: Uncoated
Surface Quality: 60-40
Clear Aperture CA (mm): 7.00
Edge Thickness ET (mm): 1.22
Center Thickness CT (mm): 3.00
f/#: 0.86
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1500

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View