

8mm MegaPixel Fixed Focal Length Lens



MegaPixel Fixed Focal Length Lenses

Stock **#56-786** **16 In Stock**

[Similar Products](#)

-

1

+

€333⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€333,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

MegaPixel Fixed Focal Length Lenses	Series:
Fixed Focal Length Lens	Type:

Physical & Mechanical Properties

Variable	Iris Option:
----------	--------------

28.20	Length (mm):
33.50	Maximum Diameter (mm):
33.5	Outer Diameter (mm):
63.00	Weight (g):
0.60	Maximum Rear Protrusion (mm):

Optical Properties	
87.00	Field of View @ Min Working Distance (mm):
42.50°	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
8.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/1.4 - f/16	Aperture (f/#):
-0.1	Maximum Distortion (%):
VIS	Lens Wavelength Range:

Sensor	
2/3"	Maximum Sensor Format:
6.20	Pixel Size (µm):

Threading & Mounting	
M30.5 x0.50	Filter Thread:
C-Mount	Mount:

Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Up to 2/3", C-Mount Lens
- Ideal for Machine Vision at an Economical Price
- 5mm to 75mm Focal Length

MegaPixel Fixed Focal Length Lenses are designed for high-resolution imaging. The lenses are ideal for machine vision applications with demanding space constraints. These lenses complement the resolution of many MegaPixel cameras with 1/2" or 2/3" formats. Low distortion and high resolution enable these economically priced lenses to produce sharp, high-contrast images compared to standard CCTV and compact lenses. MegaPixel Fixed Focal Length Lenses are available in focal lengths ranging from 5 to 75mm. Locking screws for the manual iris and focus allow these lenses to be used in high-vibration environments. Typical applications include [factory automation](#), inspection, and macro work.

Note: For [#64-869](#) 75mm FL Lens, remove focus limit screw to focus past 1.2m.

Technical Information

#56-786 8mm Megapixel Fixed Focal Length Lens



