

TECHSPEC® 8" Dia. Enhanced Aluminum, $\lambda/10$ Flat ZERODUR®



Stock **#31-394-533** 3-4 DAYS

- 1 + **€4.268,00**

ADD TO CART

Qty 1-2
€4.268,00
Qty 3+
€3.841,00
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 $\lambda/10$ (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 203.20 +0.0/-1.0
Substrate: 
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 182.88
Note: Flatness is specified as Peak to Valley
Thickness (mm): 38.10 ±2.5
Thickness Tolerance (mm): ±2.5
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference:  0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant