See all 32 Products in Family

8" x 4", Breadboard

Stock **#56-931** **20+ In Stock**

- 1 + **€106**.00

ADD TO CART

Volume Pricing	
Qty 1+	**€106,00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

English

Physical & Mechanical Properties

Thickness (inches):

0.5

Length (inches):

8.0

Width (inches):

4.0

Construction:
Black Anodized Aluminum

Flatness (inches):
0.007" per 12"

Weight (lbs):
1.5

Number of Holes:
32.00

Threading & Mounting

Mounting Threads:
(32) ¼-20 on 1" Centerline ±0.001", on 0.5" Corners

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 250:
Compliant

Product Details

- Provide Stable Platform for Experiments and Test Configurations
- 1/4-20 TPI or M6 Tapped Holes for Various Mounting
- Black Anodized Aluminum

English and Metric Breadboards utilize 1/4"-20, or M6 tapped holes spaced 1" and 25mm apart, respectively, allowing for the creation of customizable benchtop systems. These breadboards are compatible with most optics and photonics mounting solutions. They feature a black anodized finish which reduces reflections from the breadboard and back into the system. English and Metric Breadboards are available in multiple sizes, making it possible to create either compact or large, expansive systems. These breadboards are an ideal platform for any system application.

;