

8" x 8" White Advanced Illumination Side-Fired Backlight

See More by [Advanced Illumination](#)



Stock **#88-508** CLEARANCE 3-4 DAYS

-

1

+

€1.195⁰⁰

ADD TO CART

Qty 1+
€1.195,00

Volume Pricing
Request Quote

i Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

Model Number:

BX0808-WHI-IC

50,000	LED Lifetime (hours):
1.00	Number of Channels:
LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:
Backlight	Geometry:
Constant	Illumination Mode:

Physical & Mechanical Properties

267.5 L x 267.5 W x 20.1 D	Dimensions (mm):
8 x 8	Active Area (inches):

Optical Properties

White	Color:
-------	--------

Hardware & Interface Connectivity

Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855	Power Supply:
---	---------------

Environmental & Durability Factors

0 to 60	Operating Temperature (°C):
---------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

PRODUCT DETAILS

- 30% Brighter than Comparable Surface Mount Light
 - Uniform, Low Heat Illumination
- Advanced Illumination Side-Fired LED Backlights are high performance alternatives to surface mount lights. Advanced Illumination Side-Fired LED Backlights provide uniform, low heat illumination that is 30% brighter than surface mount lights of equal size. To simplify system integration, these backlights include mounting brackets and mounting channels for M6 nuts.
- Note:** Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately. Units cannot be intensity controlled.