

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Image represents #22-793: Design will vary by stock number.

Stock #22-797 3-4 DAYS



1



€350,00

ADD TO CART

Qty 1+

€350,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Manual Iris

Length (mm):
49.00

Maximum Diameter (mm):
55

Weight (g):
63

Horizontal Field of View, 1/3" Sensor:

30 - 7.1°
Maximum Image Circle (mm): 7.70
Horizontal Field of View @ Max Sensor Format: 39- 9.2°
Type: Varifocal Lens
Focal Length FL (mm): 9.00 - 40.00
Maximum Sensor Format: 1/2.3"
Working Distance (mm): 300 - ∞
Mount: CS-Mount
Aperture (f/#): F/1.5 - Closed
Lens Wavelength Range: VS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View