

## 9-90mm FL High Resolution Varifocal Lens



#68-668



Stock **#68-667** **9 In Stock**

⊖ 1 ⊕ €504.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€504,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Day-Night

**Note:**

Varifocal Lens

**Type:**

### Physical & Mechanical Properties

**Length (mm):**

93.00

Weight (g):

194.00

Diameter (mm):

45.00

## Optical Properties

Field of View @ Min Working Distance (mm):

253 - 94

Horizontal Field of View, 1/2" Sensor:

41.1° - 4.2°

Focal Length Range (mm):

9-90

Working Distance (mm):

300 - ∞

Aperture (f#):

f/1.8 - Closed

Lens Wavelength Range:

VS

## Sensor

Maximum Sensor Format:

1/2"

## Threading & Mounting

Filter Thread:

M43 x 0.75

Mount:

C-Mount

## Regulatory Compliance

Reach 191:

[Compliant](#)

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

## Product Details

CS-Mount lenses are not compatible with C-Mount cameras.

- Low Distortion and Day/Night Options
- Focal Lengths from 4.4mm - 90mm
- C-Mount Versions

Megapixel Varifocal Lenses are the ideal choice when you need a specific field of view that corresponds to a non-standard focal length. They make system integration straightforward while allowing for fine tuning, and also create the flexibility so the lenses can be integrated across multiple applications. Day/Night varifocal lenses are the perfect choice when you need to extend your imaging system into the NIR without sacrificing visible imaging. Megapixel Varifocal Lenses have C-Mount versions. The lenses feature focal lengths from 4.4 to 90mm.