

[See all 2 Products in Family](#)

9-90mm FL High Resolution Varifocal Lens



#68-668



Stock **#68-667** **9 In Stock**

-

1

+

€504^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€504,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Day-Night	Note:
Varifocal Lens	Type:
Physical & Mechanical Properties	
Length (mm):	

93.00	
194.00	Weight (g):
45.00	Diameter (mm):
Optical Properties	
253 - 94	Field of View @ Min Working Distance (mm):
41.1° - 4.2°	Horizontal Field of View, 1/2" Sensor:
9-90	Focal Length Range (mm):
300 - ∞	Working Distance (mm):
f/1.8 - Closed	Aperture (f/#):
VS	Lens Wavelength Range:
Sensor	
1/2"	Maximum Sensor Format:
Threading & Mounting	
M43 x0.75	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
Compliant	Reach 191:
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

CS-Mount lenses are not compatible with C-Mount cameras.

- Low Distortion and Day/Night Options
- Focal Lengths from 4.4mm - 90mm
- C-Mount Versions

Megapixel Varifocal Lenses are the ideal choice when you need a specific field of view that corresponds to a non-standard focal length. They make system integration straightforward while allowing for fine tuning, and also create the flexibility so the lenses can be integrated across multiple applications. Day/Night varifocal lenses are the perfect choice when you need to extend your imaging system into the NIR without sacrificing visible imaging. Megapixel Varifocal Lenses have C-Mount versions. The lenses feature focal lengths from 4.4 to 90mm.