

[All Products](#) / [Imaging Lenses](#) / [Zoom Lenses](#) / [Motorized Telephoto Varifocal Lenses](#)

[See all 6 Products in Family](#)

9.0 - 36.0mm FL, CS-Mount, P-Iris, IR Cut, Telephoto Lens



Motorized Telephoto Varifocal Lenses

Stock **#22-822** 3-4 DAYS



1



€470,00

ADD TO CART

Qty 1+

€470,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Iris Option:
Variable

Length (mm):
62.50

Maximum Diameter (mm):
54.00

Weight (g):
68.00

Horizontal Field of View @ Max Sensor Format: 39° - 10°
Type: Varifocal Lens
Maximum Sensor Format: 1/2.3"
Working Distance (mm): 2500 - ∞
Mount: CS-Mount
Aperture (f/#): f/1.5 - Closed
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View