

TECHSPEC®

9.0mm Dia. x 20mm FL, Uncoated, Plano-Convex Lens



Stock **#37-779** ☐ In Stock
[Other Coating Options](#)

-

1

+

€27,00

ADD TO CART

Qty 1-9
€27,00
Qty 10+
€24,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):

20.00 @ 587.6nm
Back Focal Length BFL (mm): 18.55
Coating: Uncoated
Substrate: N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.20 ±0.05
Edge Thickness ET (mm): 1.17
Radius R₁ (mm): 10.34
Clear Aperture CA (mm): 8.1
f/#: 2.22
Numerical Aperture NA: 0.23
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View