

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

94mm Outer Dia., Zero Aperture, Stainless Steel Leaves



Zero Series

Stock #57-599 3-4 DAYS



1



€243,00

ADD TO CART

Qty 1-4

€243,00

Qty 5+

€215,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
60.0

Outer Diameter (mm):
94.0

Construction: Anodized Aluminum Alloy, Stainless Steel Leaves
Full Angular Range of Lever (°): 98.00
Lever Length (mm): 25.00
Lever Position (mm): 4.50
Lever Size (mm): 14.00 x 2.00
Number of Leaves: Two sets of 8
Operating Temperature (°C): <400
Pin Thread & Pitch: N/A
Thickness (mm): 9.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant